

**CEEVER**



**SPRAYMASTER serie - CADET**



## TAVOLA ROTANTE

Per pezzi di piccole dimensioni e peso non superiore a 100 kg, si possono utilizzare cabine di lavaggio con piattaforma rotante.

La **rotazione** della piattaforma è ottenuta o mediante uno speciale ugello ad azione idrodinamica o meccanicamente.

L'erogazione delle soluzioni dai serbatoi avviene attraverso una o più elettropompe, le soluzioni poste così in ciclo, tornano nei propri serbatoi attraverso filtri metallici estraibili che ne permettono la pulizia.



## ROTATING PLATFORM

For small sized pieces and weight not superior to 100 kg, can be used washing booths with rotating platform.

The platform is made **rotate** by a special hydrodynamic nozzle or electromechanically.


Solutions are supplied from the reservoirs through one or more electro-pumps and the solutions made circulate return to the reservoirs through removable metal filters that make it possible to clean them.



# DATA SHEET

	SC 60 LT	SC 80 LT	SC 100 LT	SC 120 LT	SC 100 AT	SC 120 AT	UM
<b>Useful dimensions of load</b>							
Diameter	575	780	970	1170	970	1170	mm
Height	380	450	500	700	560	700	mm
load	50	100	200	300	200	300	Kg
<b>Electric pump</b>							
power	0,37	0,55	1,5	1,8	1,5	1,8	kw
pressure	2	2	2,6	3	2,6	3	bar
<b>Tank</b>							
washing	60	120	210	260	210	260	litros
<b>Heating</b>							
electric	4	4	6	8	6	8	kw
<b>Encumbrances</b>							
length	880	1100	1400	1600	1500	1700	mm
depth	800	900	1400	1600	1500	1700	mm
height	1530	1790	1920	2120	2000	2200	mm
<b>Material of construction</b>							
inox aisi 304	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
inox aisi 316	[D]	[D]	[D]	[D]	[D]	[D]	
inox aisi 316L	[D]	[D]	[D]	[D]	[D]	[D]	
<b>Endowments</b>							
Stainless steel electric pump	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
Filter of protection in stainless steel	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
Border vat gasket	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
Electric resistance in stainless steel	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
Basket rotation	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
Stainless steel aisi 304 structure	[Y]	[Y]	[Y]	[Y]	[Y]	[Y]	
<b>Endowments</b>							
Aspiration vaporise	[D]	[D]	[D]	[D]	[D]	[D]	
Contrôle automatique de niveau	[D]	[D]	[D]	[D]	[D]	[D]	
Séparateur d'huile au disque	[D]	[D]	[D]	[D]	[D]	[D]	
Garnitures spéciales	[D]	[D]	[D]	[D]	[D]	[D]	
Kit pour contaminants abrasifs	[D]	[D]	[D]	[D]	[D]	[D]	
Kit produit caustiques	[D]	[D]	[D]	[D]	[D]	[D]	
Haute pression	[D]	[D]	[D]	[D]	[D]	[D]	
Soufflage air comprimé	[D]	[D]	[D]	[D]	[D]	[D]	

[Y] - INCLUDED  
[D] - OPTIONAL  
[ND] - NO AVAILABLE







# CEEVER

Via Cesare Battisti 2  
20090 Settala  
Milan  
Italy

**PHONE**

+39.[0]2.95.77.00.24

**FAX**

+39.[0]2.95.77.03.01

**MAIL**

sales@ceever.com

**WWW.CEEVER.COM**

